



Applications and features:

- The MiniSting is a memory earth resistivity/IP meter used for vertical electrical sounding and profiling using four electrodes and manual cables.
- The instrument has a built-in rechargeable battery designed to last for a full days surveying.
- The instrument calculates and presents apparent resistivity and chargeability.
- The built-in memory can store up to 3000 measurements.

- The instrument is delivered with user manual, battery charger, utility software and data transfer cable.
- Supported electrode configurations are; resistance, Schlumberger, Wenner, dipole-dipole, pole-dipole, pole-pole, azimuthal, mise-a-la-masse, SP (absolute) and SP (gradient).
- The instrument is also used for the fall-off-potential method for ground impedance measurements and the Wenner four pin method.

MiniSting™ R1 IP, MEMORY EARTH RESISTIVITY & IP METER

TECHNICAL SPECIFICATION

Measurement modes Apparent resistivity, resistance, voltage (SP), induced polarization (IP), battery voltage

Output voltage The user can switch between high and low voltage limit for the transmitter (800 Vp-p or 320 Vp-p voltage limit).

Actual electrode voltage depends on transmitted current and ground resistivity.

Input gain rangingAutomatic, always uses full dynamic range of receiver.

 $\begin{array}{ll} \text{Input impedance} & >\!\!20~\text{M}\Omega \\ \text{Input voltage} & \text{Max } 500~\text{V} \end{array}$

SP compensation Automatic cancellation of SP voltages during resistivity measurement. Constant and linearly varying SP cancels

completely

Type of IP measurement Time domain chargeabilitiy (M), six time slots measured and stored in memory

IP current transmission ON+, OFF, ON-, OFF IP time cycles 1 s, 2 s, 4 s and 8 s

Measure cycles Running average of measurement displayed after each cycle. Automatic cycle stop when reading errors fall below

user set limit or user set max cycles are done.

Cycle time Basic measure time is 1.2, 3.6, 7.2 or 14.4 s as selected by user via keyboard, auto ranging and commutation

adds about 1.4 s.

Signal processing Continuous averaging after each complete cycle. Noise errors calculated and displayed as percentage of reading.

Reading displayed as resistance (ΔVII) and apparent resistivity (Ωm). Resistivity is calculated using user entered

electrode array coordinates.

Noise suppression Better than 100 dB at f>20 Hz

Better than 120 dB at power line frequencies (16 2/3, 20, 50 and 60 Hz).

Total accuracy Better than 1% of reading in most cases (lab measurements). Field measurement accuracy depends on ground

noise and resistivity. Instrument will calculate and display running estimate of measuring accuracy. Calibration is done digitally by the microprocessor based on correction values stored in memory.

System calibration Calibration is done digitally by the microprocessor based on correction values stored in memory.

Supported configurations Resistance, Schlumberger, Wenner, dipole-dipole, pole-dipole, pole-pole, azimuthal, mise-a-la-masse, SP

(absolute) and SP (gradient).

Data storage Full resolution reading average and error are stored along with user entered coordinates and time of day for each

measurement. Storage is effected automatically.

Memory capacity More than 3000 measuring points can be stored in internal memory.

Data transmissionRS-232C channel included to dump data from instrument to PC on user command.

User controls

RS-232C channel included to dump data from instrument to PC on user command.

20 key tactile, weather proof keyboard with numeric entry keys and function keys.

On/off switch

Measure button, integrated within main keyboard.

LCD night light switch (push to light).

Display Alphanumeric LCD display (4 lines x 20 characters) with night light.

Connectors 4 banana plug, pole screws for current and potential electrodes. 3-pole KPT connector for external power, 10-pole

KPT connector for RS-232C and synchronization connections.

Power supply 12V, 4.5 Ah NiMH built-in rechargeable battery. External power connector on front panel, the instrument

automatically selects external battery if present.

Operating time Depends on conditions, internal circuitry in auto mode adjusts current to save energy. At 20 mA output current and

10 k Ω electrode resistance more than 2000 cycles are available from a fully charged battery pack.

Battery charger Dual stage charger with switchable input (115/230 V AC @ 50/60 cycles)

Weight 6.6 kg (14.5 lb.)

Dimensions Width 255 mm (10"), length 255 mm (10") and height 123 mm (5").

Advanced Geosciences, Inc.

2121 Geoscience Dr., Austin Texas 78726, USA

Brazil: Tel. 21 3507-766

E-mail: info@alphageofisica.com.br

Web site: http://www.alphageofisica.com.br